

**Garant**

**Toolholder for imperial profile broaching tools  $\varnothing d = 16$  mm, Shank  $\varnothing DS$ : 1.1/4in**

**Order data**

Order number	293076 1.1/4
GTIN	4062406129057
Item class	29K

**Description****Suitable for:**

CNC and conventional machines.

**Optional extras:**

Positioning aid (No. 293000) and pin wrench (No. 293006).

Drive-out tang for MT shanks can be ordered under No. 293008 in the sizes MK2, MK3 and MK4.

**Note:**

- **Caution: Always use appropriate slotting tool  $\varnothing$ .**
- **Other shank connections on request.**

**Technical description**

L	76 mm
Shank length $L_s$	50 mm
Shank type	Plain shank
$\varnothing D$	58 mm

Ø d	16 mm
Shank size	1,1/4 in
Through-coolant	no
Type of product	Keyway broaching and profile slotting tool

---

## Accessories

Pin spanner for holder Ø 5 mm	293006 5
Pin spanner for holder Ø 16 mm	293006 16
Pin spanner for holder Ø 12 mm	293006 12
Pin spanner for holder Ø 8 mm	293006 8