



Digital universal caliper DIGI ULISSE I/E, Measuring range: 500mm



Order data

Order number	417700 500
GTIN	2050001780072
Item class	46P

Description

Version:

Digital universal caliper for a variety of internal and external measurements, with exchangeable measuring tips.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Digital caliper including 1 battery No. 081560 size CR2032. Interchangeable measuring tips with ball \varnothing 3 mm and clamping sleeve with M2.5 internal thread.

Optional extras:

For size 400 - 650 all replacement and special contact points No. 434900 - 4910 with M2.5 thread can be used, data cable No. 498948.

Note:

Other measuring tips on request.

Technical description

Jaw length	103 mm
IP Index of Protection	IP 67
Measuring range inside	42 - 500 mm
Measuring range outside	0 - 420 mm
Ball \varnothing measuring tips	3 mm
Calibration	A1

Measuring range	0 - 500 mm
Scale divisions	0.01 mm
Error limit	0.03 mm
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
Power supply	Battery-powered
Standard	Manufacturer's standard
Reversible reading	mm / inch
Interface	USB interface
Interface	RS232 interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 500 mm	021000 500
DAkkS calibrationCalipers / depth gauges maximum measuring range 500 mm	021010 500

Accessories

Carbide contact point Type 18/3	434910 18/3
Steel contact point Type 18/3	434900 18/3
Connection cable Type USB2	498948 USB2
Accessories for calipers Type TAST	417701 TAST
Button cell / special battery Battery type CR2032	081560 CR2032
Accessories for calipers Type BUCHSE	417701 BUCHSE

Connection cable Type R2

498948 R2