

ejendals

Pair of welder's safety gloves Tegera® 126A, Glove size: 10



Order data

Order number	094123 10
GTIN	7340118312255
Item class	04R

Description

Version:

Tegera® 126A. Unlined welder's gloves with **outstanding touch sensitivity** (finger tip sensitivity 5 as specified in EN 420) and excellent close fit. Reinforced index finger and seams reinforced with Kevlar® thread, for use in demanding working environments. Resistant to 100 °C contact temperature.

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Protection category	Category III
Type of glove	Welder's gloves
Glove size	10
Glove characteristics	Flame resistance stage 4
Application	reusable
Length	310 mm

Backing material	Full-grain goatskin
Coating variant	No coating
Contents	12
Material	Full-grain goatskin
Application range	Heavy Duty
Contact heat up to	100 °C
EN 388	2111X
EN 407	412X4X
EN 12477	Type B
Welding processes	WIG
Colour	yellow / white
Standard	EN 407
Type of product	Welder's gloves