



COLOUR MATCH LED true colour work lamps, Type: PEN



Order data

Order number	081513 PEN
GTIN	5708997351178
Item class	08C

Description

Version:

COLOUR MATCH. Special LED with high CRI value for **perfect colour reproduction** and extremely long LED working life. Perfect for all painting, polishing, cleaning and preparation work. Designed for use in paint shops. **Exchangeable glass lens** and resistant to all types of solvent, even when cleaned every day. **MATCHPEN.** Small portable pen torch with focus function for bundled and concentrated illumination between 10° and 70°. Ideal for detecting scratches and scuffs during quality control.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Supplied with 2 × AAA batteries.

Technical description

Light colour	true colour
Number of batteries contained	2
Illumination	100 lm
Power supply	Battery powered
Battery type	Micro, AAA
Overall width	16 mm
Illumination time	2 h
IP Index of Protection	IP 54

CRI value	95
Overall length	150 mm
Weight	60 g
ATEX zone	no
Manufacturer's designation	MINI
Type of product	Work lamp

Accessories

Lithium-metal batteries International size LR3	081559 LR3
Alkaline-manganese batteries International size LR3	081552 LR3
Alkaline-manganese batteries International size LR3	081551 LR3
Alkaline-manganese batteries International size LR3	081561 LR3
Alkaline-manganese batteries International size LR3	081554 LR3
Alkaline-manganese batteries International size LR3	081553 LR3