

HEDI

Cable drum plastic, Type: 40B2



Order data

Order number	081125 40B2
GTIN	
Item class	08B

Description

Version:

Hedi® cable drums stand for “Made in Germany” quality and a long service life. The drum body is specially designed to optimally guide the cable. The integrated rotation stop switch prevents accidental drum rotation. All cable drums are equipped with thermal cut-out switches. With spring-loaded covers. For **continuous** use in the open air. Satisfies DGUV I 203-005 (formerly BGI 600).

PU armoured cable Plus.

Conductor cross-section 2.5 mm. Personal protection PRCD-S mounted on the cable, triggering current 30 mA, response time ≤ 30 ms.

Function:

IP44: Protected against splashed water from all directions and protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away.

Technical description

Type	40B2
Cable length	40 m
Material cable	Armoured cable

AC supply voltage	250 V
Rated power unrolled	3500 (16 A) W
Cable structure	3G2.5
Cable class	H07BQ-F
IP Index of Protection	IP 44
impact-resistant and splash-proof	Category 2 (K2) to BGI
Material of body	Plastic
Number of sockets	3
Power supply	Mains operated
Diagnostic system present	yes
Type of product	Cable drum