

HEDI

Cable drum plastic, Type: 25B2



Order data

Order number	081136 25B2
GTIN	4003644000555
Item class	08B

Description

Version:

Hedi® cable drums stand for “Made in Germany” quality and a long service life. The drum body is specially designed to optimally guide the cable. The integrated rotation stop switch prevents accidental drum rotation. All cable drums are equipped with thermal cut-out switches.

Sturdy cable drum of high-impact plastic with **thermal overload protection**.

- **400 V CEE input plug 16 A.**
- **400 V CEE output plug 16 A with spring-loaded cover.**
- **Two 250 V standard Schuko sockets with spring-loaded covers.**
- **Conductor cross-section 2.5 mm.**

Certified for continuous exterior use and for use in humid environments.

Satisfies the specifications of DGUV I 203-006 (formerly BGI 608) and DGUV I 203-005 (formerly BGI 600). **Conductor cross-section 2.5 mm.**

PU armoured cable Plus.

Function:

IP44: Protected against splashed water from all directions and protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away.

IP Index of Protection: IP 44

impact-resistant and splash-proof: Category 2 (K2) to BGI

Rated power unrolled: 5500 (16 A) W

Cable class: H07BQ-F

Cable structure: 5G2,5
Material cable: Armoured cable
Cable length: 25 m

Technical description

Type	25B2
AC supply voltage	400 V
Material cable	Armoured cable
Cable structure	5G2,5
Rated power unrolled	5500 (16 A) W
Cable length	25 m
Cable class	H07BQ-F
IP Index of Protection	IP 44
impact-resistant and splash-proof	Category 2 (K2) to BGI
Material of body	Plastic
Power supply	Mains operated
Type of product	Cable drum