

HEDI

Cable drum plastic for F, B, PL and CZ, Type: 25B2



Order data

Order number	081138 25B2
GTIN	
Item class	08B

Description

Version:

Hedi® cable drums stand for “Made in Germany” quality and a long service life. The drum body is specially designed to optimally guide the cable. The integrated rotation stop switch prevents accidental drum rotation. All cable drums are equipped with thermal cut-out switches.

Sturdy cable drum of high-impact plastic with **thermal overload protection**.

- **400 V CEE input plug 16 A.**
- **400 V CEE output plug 16 A with spring-loaded cover.**
- **Two 250 V standard Schuko sockets with spring-loaded covers.**
- **Conductor cross-section 2.5 mm.**

Certified for continuous exterior use and for use in humid environments.

With 250 V sockets for **F, B, PL, and CZ. Conductor cross-section 2.5 mm.**

PU armoured cable Plus.

Function:

IP44: Protected against splashed water from all directions and protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away.

Technical description

Type	25B2
------	------

Number of sockets 400 V/16 A	1
AC supply voltage	400 V
Cable length	25 m
Number of sockets 230 V	2
Cable class	H07BQ-F
Cable structure	5G2,5
Material cable	Armoured cable
Rated power unrolled	5500 (16 A) W
IP Index of Protection	IP 44
Material of body	Plastic
Power supply	Mains operated
Type of product	Cable drum