

**Workbench with 3 drawers and 2 swing doors, Worktop length: 2000mm****Order data**

Order number	929560 2000
GTIN	4062406130053
Item class	92W

Description**Version:**

- **Worktop 40 mm thick, non-warping beech marine ply, finished with clear UV varnish.**
- **Frame - welded sheet metal.**
- **Drawers of sheet metal with low-friction rollers of Delrin.**
- **Sheet metal doors with plastic grips, opening angle 180° and self-closing hinges.**
- **Central cylinder lock with 2 keys.**

Fitted with:

Drawer front height (centre): 180; 180; 180

Door height (left) mm: 540

Door height (right): 540

Optional extras:

For suitable storage shelf see No. 929581.

Colour:

Body RAL 7035 light grey, fronts anthracite RAL 7016, **powder-coated, internal shelves and storage shelves on top galvanized.**

Note:

Other colours available for fronts: RAL 7035 light grey, RAL 5005 signal blue. No special paint finishes available.

Technical description

Door height (right)	540 mm
Support cabinet width	1775 mm

Height	850 mm
Worktop length	2000 mm
Number of drawers	3
Door height (left)	540 mm
Worktop thickness	40 mm
Weight	117 kg
Workbench/desk load capacity - maximum distributed load (on wood)	900 kg
Support cabinet depth	630 mm
Material of worktop	Beech marine ply
Worktop depth	700 mm
Surface worktop	clear varnished
Workbench can be locked centrally	yes
Drawer usable width	490 mm
Workbench for installation in a row	no – the worktop projection is too large
Drawer usable depth	520 mm
Material thickness	1.5 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	100 kg
Insert thickness	40 mm
Drawer runner extension (partial/full extension)	90 %
Door opening angle	180 degrees
Height adjustment	20 mm
Cylinder lock	modular barrel
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Workbench

Accessories

Barrel sleeve 225-010-9 without lock barrel

914202