

**Workbench with 2 drawers and 3 swing doors, Worktop length: 2000mm****Order data**

Order number	929550 2000
GTIN	4062406130046
Item class	92W

**Description****Version:**

- **Worktop 40 mm thick, non-warping beech marine ply, finished with clear UV varnish.**
- **Frame - welded sheet metal.**
- **Drawers of sheet metal with low-friction rollers of Delrin.**
- **Sheet metal doors with plastic grips, opening angle 180° and self-closing hinges.**
- **Central cylinder lock with 2 keys.**

**Fitted with:**

Drawer front height (left) mm: 180  
Drawer front height (right) mm: 180  
Door height (left) mm: 360  
Door height (centre) mm: 540  
Door height (right) mm: 360

**Optional extras:**

For suitable storage shelf see No. 929581.

**Colour:**

Body RAL 7035 light grey, fronts anthracite RAL 7016, **powder-coated, internal shelves and storage shelves on top galvanized.**

**Note:**

Other colours available for fronts: RAL 7035 light grey, RAL 5005 signal blue. No special paint finishes available.

**Technical description**

Worktop thickness	40 mm
-------------------	-------

Worktop length	2000 mm
Material of worktop	Beech marine ply
Drawer usable depth	520 mm
Door height (right)	360 mm
Support cabinet width	1775 mm
Height	850 mm
Workbench/desk load capacity - maximum distributed load (on wood)	900 kg
Surface worktop	clear varnished
Weight	113 kg
Support cabinet depth	630 mm
Workbench for installation in a row	no – the worktop projection is too large
Workbench can be locked centrally	yes
Door height (left)	360 mm
Number of drawers	2
Worktop depth	700 mm
Drawer usable width	490 mm
Material thickness	1.5 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	100 kg
Insert thickness	40 mm
Drawer runner extension (partial/full extension)	90 %
Door opening angle	180 degrees
Height adjustment	20 mm
Cylinder lock	modular barrel
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Workbench

## Accessories

Barrel sleeve 225-010-9 without lock barrel

914202