

## ejendals

### Pair of gloves Tegera® 882, Glove size: 10



#### Order data

Order number	094366 10
GTIN	7392626040229
Item class	04R

#### Description

##### Version:

Tegera® 882. Synthetic gloves with full nitrile foam coating and a good grip. The close fit and good finger tip sensitivity ensure that the gloves are outstandingly suitable for precision mechanical work in **moist or oily environments. Contact temperature up to 100 °C.**

##### Standard:

EN 388; EN 420

##### Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

#### Technical description

Protection category	Category II
Glove size	10
Type of glove	Multi-purpose gloves
Contents	12
EN 388:2016	4121X
EN 407	X1XXXX

Backing material	Nylon
Coating	Nitrile foam
Coating variant	Full coating
Application range	All-round
Application range	Precision
Colour	black
Knitted technology	15G
Contact heat up to	100 °C
Application	reusable
Type of product	Multi-purpose gloves