

## Individual stainless steel test pin Tolerance class 1, Type: 6



### Order data

Order number	483914 6
GTIN	2050002038387
Item class	48A

### Description

#### Version:

Test pin of stainless and acid-resistant material, hardened (58-62 HRC) and tempered. Surface ground and lapped. From  $\varnothing$  1.50 the dimension is marked on the sleeve; from  $\varnothing$  3.00 on the end face. From  $\varnothing$  1.00 mm, one end chamfered.

#### Note:

When ordering, **please additionally state the desired  $\varnothing$** , e.g. No. 483914 size 5 **10.08**.

### Technical description

Pitch	0.01 mm
Gauging pin length	70 mm
Nominal size	12 - 13.99 mm
Calibration	L5
Standard	DIN 2269
Type of product	Test pin

### Services

DAkkS calibration Test pin maximum $\varnothing$ 20	028260 20
Calibration Test pin maximum $\varnothing$ 20	028240 20