

**KÄRCHER**
**Wet and dry vacuum cleaner, Manufacturer's designation: NT65APME**

**Order data**

Order number	078521 NT65APME
GTIN	4039784727366
Item class	07C

**Description**
**Version:**

Powerful all-purpose **wet and dry cleaners** with high suction power and compact design, hose storage, and accessory storage on the cleaner. **Automatic shut-down** when the maximum filling level is reached in the container.

- **Folded filter enables wet and dry suction without removing the filter.**
- **The Tact automatic filter cleaning system permits uninterrupted work in combination with low maintenance costs and long working life of the filter.**
- **The central rotary switch permits easy switching between the suction programs.**
- **Professional dual-motor industrial vacuum cleaner with stainless steel tank.**
- **Robust 65-litre container with bumpers and metal castors.**
- **Practically constant suction power thanks to efficient AP semi-automatic filter cleaning by manually triggered air pulse.**

**Supplied with:**

Suction hose with elbow, metal suction tube 2x0.5 m, floor nozzle, and crevice nozzle, flat fold filter or paper filter bag.

**Note:**

Industrial vacuum cleaner No. 078522 for materials that are oily or contain oil.

Power consumption: 2760 W

Container volume: 65 l

Connection width: 40 mm

Length: 600 mm

Width: 480 mm

Height: 920 mm

## Technical description

Weight	23 kg
Air flow volume	2×74 l/s
Suction hose length	4 m
Length	600 mm
Power consumption	2760 W
Height	920 mm
Filter cleaning	ApClean semi-automatic filter cleaning
Operating noise	73 dB(A)
Width	480 mm
Container volume	65 l
Dust class – vacuum cleaner	L
Vacuum	254 mbar
Number of turbines	2
Cable length	10 m
Manufacturer's designation	NT65APME
Connection width	40 mm
Filter system	Fan-fold filter
Special features	Stainless steel tank
Power supply	Mains operated
Type of product	Wet and dry vacuum cleaners

## Accessories

Flat fold filter suitable for vacuum cleaner type NT65	072809 NT65
--	-------------

Swarf set oil-resistant Connection width DN40	078526 DN40
Rubber oblique-end nozzle Connection width DN40	078527 DN40
Filter bag set 5 pieces suitable for vacuum cleaner type NT65	072808 NT65
Crevice nozzle, narrow, 13 mm Connection width DN40	078528 DN40