



LED rechargeable work lamp, Type: MINI-PRO



Order data

Order number	081516 MINI-PRO
GTIN	5708997356920
Item class	08C

Description

Version:

LED rechargeable work lamp with high-power LEDs for high light output. With fold-out swivel support hook and powerful attachment magnet. New generation of the **MINI-MAG** version, powerful spotlight and main light, with charge indicator at the front.

High-performance **COB LED technology for extremely bright homogeneous lighting of an area at two levels of brightness.**

Steplessly dimmable.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Supplied with USB charging cable.

Technical description

Bulb	LED module
Number of rechargeable batteries contained	1
Battery capacity	1.2 Ah

Type of rechargeable battery	Lithium-ion
Illumination	20 - 200 lm
Battery voltage	3.7 V
Power supply	Rechargeable battery powered
Illumination time	2 - 20 h
Overall length	202 mm
IP Index of Protection	IP 54
Overall width	40 mm
Weight	143 g
ATEX zone	no
Manufacturer's designation	MINIMAG PRO
Type of product	Work lamp

Accessories

Li-ion battery Battery capacity 1200 mAh	081431 1200
--	-------------