



LED rechargeable work lamp, Type: MAG-PRO



Order data

Order number	081516 MAG-PRO
GTIN	5708997356906
Item class	08C

Description

Version:

LED rechargeable work lamp with high-power LEDs for high light output. With fold-out swivel support hook and powerful attachment magnet. New generation of the **MAG3** version, with exceptionally high light output, very powerful spotlight and main light, with charge indicator at the front.

High-performance **COB LED technology for extremely bright homogeneous lighting of an area at two levels of brightness.**

Steplessly dimmable.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Supplied with USB charging cable.

Technical description

Type of rechargeable battery	Lithium-ion
Battery capacity	2.6 Ah

Number of rechargeable batteries contained	1
Illumination	60 - 600 lm
Power supply	Rechargeable battery powered
Battery voltage	3.7 V
Bulb	LED module
IP Index of Protection	IP 54
Overall width	70 mm
Illumination time	1.5 - 15 h
Overall length	270 mm
Weight	312 g
ATEX zone	no
Manufacturer's designation	_MAG-PRO
Type of product	Work lamp