

**LED area floodlight, 230 V, Power consumption: 65W****Order data**

Order number	081267 65
GTIN	5708997356371
Item class	08C

Description**Version:**

Non-shadowing and non-dazzle version with wide spread of light.
High-power 360° work lamp with Schuko socket. The lamp can be hung anywhere on a sturdy hook, and stood directly on the workbench.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Suitable for:

Three-leg stand No. 081252 size 1.35-3.

Technical description

Bulb	LED lamp
Power supply	Mains-powered
Illumination	6000 lm
Power consumption	65 W
Beam dispersion angle adjustable	360 degrees

Weight	3500 g
Light colour	6000 K
IP Index of Protection	IP 54
Nominal voltage	220 - 240 V
Overall length	305 mm
Overall width	199 mm
Overall height	199 mm
Connection cable length	5 m
ATEX zone	no
Product name attribute	230 V
Type of product	Area light