

**Garant****Pair of gloves, Glove size: 10****Order data**

Order number	094325 10
GTIN	4062406131074
Item class	01H

**Description****Version:**

All constituent parts including carrier material and also coating are **free of silicone** (tested by the Fraunhofer Institut). They are thus ideally suitable for use in operating areas in the automobile industry or paint shops.

Silicone-free multi-purpose gloves for light industrial applications, with very high resistance to abrasion but nevertheless unusually good comfort characteristics. Nylon backing with Spandex 15-gauge knitted technology and a tough polyurethane coating.

**Standard:**

EN 388, EN ISO 21420

**Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

**Technical description**

Type of glove	Multi-purpose gloves
Glove size	10
Protection category	Category II

Contents	12
Glove characteristics	LABS free
Glove characteristics	Silicone-free
EN 388	3121A
Backing material	Nylon
Coating	PU
Coating variant	The palms of the hands
Application range	Precision
Colour	blue / orange
Knitted technology	15G
Application	reusable
Cut protection class	FG
Type of product	Multi-purpose gloves