

**Garant****Pair of gloves Cut B, Glove size: 7****Order data**

Order number	094405 7
GTIN	4062406131098
Item class	01H

**Description****Version:**

All constituent parts including carrier material and also coating are **free of silicone** (tested by the Fraunhofer Institut). They are thus ideally suitable for use in operating areas in the automobile industry or paint shops.

Silicone-free cut-resistant gloves with very good fit and light weight. Due to the high degree of finger freedom highly suitable for precise handling of sharp-edged parts. Special yarn with Spandex **18-gauge knitted technology** and a tough polyurethane coating.

**Standard:**

EN 388, EN ISO 21420

**Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

**Technical description**

Protection category	Category II
Type of glove	Multi-purpose gloves
Glove size	7

Contents	12
Glove characteristics	LABS free
Glove characteristics	Silicone-free
EN 388	4X42B
Backing material	Nylon / special yarn / Spandex
Coating	PU
Coating variant	The palms of the hands
Application range	Precision
Length	180 mm
Colour	grey / orange
Knitted technology	18G
Application	reusable
Cut protection class	B
Type of product	Multi-purpose gloves