

## PRYOR

**Numeral punch set, 10 pieces Normal script 0 – 9, Character height: 3mm**



### Order data

Order number	085405 3
GTIN	5022044000186
Item class	08W

### Description

#### Version:

Made of hard and tough steel with particularly precise machine engraving and depth tolerance; accurately centred. Calibrated shank, through hardened. Striking head enhancement for safe working. Supplied in a plastic case.

**High performance precision punches**, chemically nickel-plated, very long service life.

**Normal script**; i. e. the punched character can be read directly on the component.

#### Application:

For punching into materials with a **strength up to 1200 N/mm<sup>2</sup>**.

#### Spare part:

Individual number punches under No. 085411 size font height/number, e. g. No. 085411 size 3/1.

Individual letter punches under No. 085431 size font height/character, e.g. No. 085431 size 3/A.

#### Note:

Other hand and machine punches of all types, such as punches with a company's logo etc., are available on request.

### Technical description

Shank thickness	6.35
-----------------	------

Depth limitation	yes
overall length	63.5 mm
Character height	3 mm
Type of product	Hand punch

## Accessories

Number punch – individual Normal script 0 – 9 Font height (mm) / characters 3/3	085411 3/3
Punch holder Type GRIP	085475 GRIP
Number punch – individual Normal script 0 – 9 Font height (mm) / characters 3/9	085411 3/9
Number punch – individual Normal script 0 – 9 Font height (mm) / characters 3/0	085411 3/0
Number punch – individual Normal script 0 – 9 Font height (mm) / characters 3/7	085411 3/7
Number punch – individual Normal script 0 – 9 Font height (mm) / characters 3/6	085411 3/6
Number punch – individual Normal script 0 – 9 Font height (mm) / characters 3/5	085411 3/5
Number punch – individual Normal script 0 – 9 Font height (mm) / characters 3/2	085411 3/2
Number punch – individual Normal script 0 – 9 Font height (mm) / characters 3/1	085411 3/1
Number punch – individual Normal script 0 – 9 Font height (mm) / characters 3/4	085411 3/4
Number punch – individual Normal script 0 – 9 Font height (mm) / characters 3/8	085411 3/8