



UV work lamp with rechargeable battery, Type: UV-LIGHT



Order data

Order number	081525 UV-LIGHT
GTIN	5708997358016
Item class	08C

Description

Version:

UV CURING. Special LED lamps for quick curing of UV-curing primers, fillers, paints and also adhesives. Flexible cordless LED hand-held lamp for UV curing of small and medium-sized areas. Curing area Ø 10 cm. Supplied with charging station, Li-ion battery (2.6 Ah).

Function:

IP30: Protected against penetration by foreign bodies with $\varnothing > 2.5$ mm, however tools and wires should be kept away, and offers no protection against water.

Technical description

Battery voltage	3.7 V
IP Index of Protection	IP 30
Illumination time	1.5 h
Battery capacity	2.6 Ah
Number of rechargeable batteries contained	1
Type of rechargeable battery	Lithium-ion

Overall length	190 mm
Wavelength of UV radiation	390 nm
Power supply	12
ATEX zone	no
Type of product	Work lamp