



UV work lamp with rechargeable battery, Type: NOVA-UV



Order data

Order number	081525 NOVA-UV
GTIN	4062406131159
Item class	08C

Description

Version:

UV CURING. Special LED lamps for quick curing of UV-curing primers, fillers, paints and also adhesives. Rechargeable floodlight for UV curing of large areas. Curing area Ø 25 cm. Supplied with charger, Li-ion battery (5.4 Ah), integral power bank with USB port.

Function:

IP30: Protected against penetration by foreign bodies with Ø > 2.5 mm, however tools and wires should be kept away, and offers no protection against water.

Technical description

IP Index of Protection	IP 30
Battery capacity	5.4 Ah
Illumination time	1.5 h
Battery voltage	3.7 V
Manufacturer's designation	NOVA-UV
Number of rechargeable batteries contained	1

Type of rechargeable battery	Lithium-ion
Power supply	12
Overall length	163 mm
Wavelength of UV radiation	390 - 400 nm
ATEX zone	no
Type of product	Work lamp