

**SPS LED cordless work lamp, Power consumption: 30 W****Order data**

Order number	081262 30
GTIN	5708997360002
Item class	08C

Description**Version:**

Sturdy LED work lights with shock-resistant aluminium casing and rubber protective surround.

- **Soft non-shadowing anti-glare lamp, with low heat emission.**
- **High light output, low energy consumption, long working life.**
- **Certified for exterior use and for use in humid environments.**

NOVA work lamps with integral carrying handle. High-performance COB-LED with 5-step dimmer function, pivoting.

New generation of NOVA work lamps with patented SPS* battery system and Bluetooth, incl. replacement battery and charger. *SPS = Scangrip Power Solution: The lamp can be operated optionally with battery or direct connection to the power supply. The charger can be used directly as a power supply for the lamp. Integral reserve battery: The lamp remains in operation for up to 1 hour at 1000 Lumen output – without a battery, without a mains cable.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

IP Index of Protection: IP 67

ATEX zone: no

Illumination: 400 - 4000 lm

Working life: 1 h

CRI value: 80

Number of rechargeable batteries contained: 2

Type of rechargeable battery: Lithium-ion

Technical description

Battery voltage	11.1 V
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Colour temperature	6000 K
IP Index of Protection	IP 67
Number of rechargeable batteries contained	2
Working life	1 h
ATEX zone	no
Illumination	400 - 4000 lm
Battery capacity	4 Ah
Overall length	240 mm
Overall width	230 mm
Overall height	104 mm
CRI value	80
Weight	1970 g
Type of product	Work lamp

Accessories

Three-leg stand Height 1,35-3 m	081252 1,35-3
---------------------------------	---------------