

## ejendals

### Pair of gloves Tegera® 8805 Infinity, Glove size: 7



#### Order data

Order number	094561 7
GTIN	7340118319339
Item class	04R

#### Description

##### Version:

Tegera® 8805 Infinity. Anatomically shaped cut-resistant gloves with **18-gauge knitting technology** for optimum fit and good finger tip sensitivity. High-quality nitrile foam water-based PU coating ensures good grip capability. With reinforced thumb joint. For **contact heat up to 100°C. Suitable for touch screens**. Approved for handling foodstuffs. In addition the gloves are **silicone-free** and have been dermatologically tested.

##### Standard:

EN 388; EN ISO 21420

##### Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

#### Technical description

Protection category	Category II
Glove size	7
Type of glove	Cut-resistant gloves
Contents	6

Glove characteristics	Suitable for touch screens
Glove characteristics	Foodstuffs certified
Glove characteristics	DMF-free
Knitted technology	18G
Clothing standard	Oeko-Tex Standard 100
EN 388	4X41B
EN 407	X1XXXX
Backing material	Nylon, steel fibres, carbon
Coating	Nitrile foam/water-based PU
Coating variant	The palms of the hands
Application range	All-round
Colour	black / grey / yellow
Standard	EN 407
Contact heat up to	100 °C
Application	reusable
Cut protection class	B
Type of product	Cut-resistant gloves