

Garant GRIDLINE

Drawer with one-handed individual drawer release system, 75 kg, 20×20G, Drawer front height: 100mm



Order data

Order number	930534 100
GTIN	4062406131180
Item class	9GK

Description

Version:

100% full extension drawers with differential runners. Aluminium handle with labelling strips that can be exchanged and rewritten.

Slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

With **one-handed individual drawer release system** prevents the opening of drawers during transport. Absolutely necessary for all roller cabinets.

Suitable for:

Tool cabinet casing 24×24G No. 930525.

Supplied with:

Drawers each complete with 1 pair drawer runner rails.

Colour:

Drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Weight	10 kg
Usable height	75 mm
Drawer/pull-out shelf load capacity	75 kg
Individual drawer release system	One-hand
Drawer usable area in G	20×20

Front height	100 mm
Usable width in G	20
Usable depth in G	20
Application range	Assembly trolley
Usable depth	500 mm
Usable width	500 mm
with individual drawer release system	yes
Material thickness	1.2 mm
Drawer runner extension (partial/full extension)	100 %
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	20×20G
Type of product	Drawer

Accessories

One-hand individual drawer release system Drawer usable width in G 20	951020 20
Labelling strip set 10 pieces Drawer usable width in G 20	951030 20
Pack of PVC covers for handles 10 pieces Drawer usable width in G 20	951032 20
Handle end caps 20 pieces Type 10	951025 10