

Garant GRIDLINE

## Drawer with one-handed individual drawer release system, 75 kg, 20×20G, Drawer front height: 150mm



### Order data

Order number	930534 150
GTIN	4062406131203
Item class	9GK

### Description

#### Version:

**100% full extension drawers** with differential runners. Aluminium handle with labelling strips that can be exchanged and rewritten.

Slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

With **one-handed individual drawer release system** prevents the opening of drawers during transport. Absolutely necessary for all roller cabinets.

#### Suitable for:

Tool cabinet casing 24×24G No. 930525.

#### Supplied with:

Drawers each complete with 1 pair drawer runner rails.

#### Colour:

Drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

### Technical description

Weight	11 kg
Drawer usable area in G	20×20
Usable height	125 mm
Front height	150 mm
Drawer/pull-out shelf load capacity	75 kg

Individual drawer release system	One-hand
Usable width in G	20
Usable depth in G	20
Application range	Assembly trolley
Usable width	500 mm
Usable depth	500 mm
with individual drawer release system	yes
Material thickness	1.2 mm
Drawer runner extension (partial/full extension)	100 %
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	20×20G
Type of product	Drawer

## Accessories

Labelling strip set 10 pieces Drawer usable width in G 20	951030 20
One-hand individual drawer release system Drawer usable width in G 20	951020 20
Handle end caps 20 pieces Type 10	951025 10
Pack of PVC covers for handles 10 pieces Drawer usable width in G 20	951032 20