

Garant GRIDLINE

**Drawer with one-handed individual drawer release system, 75 kg, 36×20G,
Drawer front height: 50mm****Order data**

| | |
|--------------|---------------|
| Order number | 930744 50 |
| GTIN | 4062406131586 |
| Item class | 9GK |

Description**Version:**

100% full extension drawers with differential runners. Aluminium handle with labelling strips that can be exchanged and rewritten.

Slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

With **individual drawer release system** prevents the opening of drawers during transport.

Absolutely necessary for all roller cabinets.

Load capacity 75 kg.

Suitable for:

Tool cabinet casing 40×24G No. 930735.

Supplied with:

Drawers each complete with 1 pair drawer runner rails.

Colour:

Drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated**. **Drawer body not configurable, always RAL 7035 light grey.**

Technical description

| | |
|-------------------------------------|----------|
| Drawer/pull-out shelf load capacity | 75 kg |
| Drawer usable area in G | 36×20 |
| Usable height | 25 mm |
| Front height | 50 mm |
| Individual drawer release system | One-hand |
| Weight | 13 kg |

| | |
|--|--|
| Usable width in G | 36 |
| Usable depth in G | 20 |
| Application range | Assembly trolley |
| Usable width | 900 mm |
| Usable depth | 500 mm |
| with individual drawer release system | yes |
| Material thickness | 1.2 mm |
| Drawer runner extension (partial/full extension) | 100 % |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Drawer usable width × usable depth in G | 36×20G |
| Type of product | Drawer |

Accessories

| | |
|---|-----------|
| Handle end caps20 pieces Type 10 | 951025 10 |
| Labelling strip set10 pieces Drawer usable width in G 36 | 951030 36 |
| Pack of PVC covers for handles10 pieces Drawer usable width in G 36 | 951032 36 |
| One-hand individual drawer release system Drawer usable width in G 36 | 951020 36 |