

Garant GRIDLINE

Drawer with one-handed individual drawer release system, 200 kg, 26×20G, Drawer front height: 300mm



Order data

| | |
|--------------|---------------|
| Order number | 930636 300 |
| GTIN | 4062406131579 |
| Item class | 9GK |

Description

Version:

100% full extension drawers with differential runners. Aluminium handle with labelling strips that can be exchanged and rewritten.

Slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

With **individual drawer release system** prevents the opening of drawers during transport.

Absolutely necessary for all roller cabinets.

Load capacity 200 kg.

Suitable for:

Tool cabinet casing 30×24G No. 930625.

Supplied with:

Drawers each complete with 1 pair drawer runner rails.

Colour:

Drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

| | |
|----------------------------------|----------|
| Usable height | 275 mm |
| Drawer usable area in G | 26×20 |
| Weight | 19 kg |
| Individual drawer release system | One-hand |

| | |
|--|--|
| Front height | 300 mm |
| Drawer/pull-out shelf load capacity | 200 kg |
| Usable depth in G | 20 |
| Usable width in G | 26 |
| Application range | Assembly trolley |
| Usable depth | 500 mm |
| Usable width | 650 mm |
| with individual drawer release system | yes |
| Material thickness | 1.2 mm |
| Drawer runner extension (partial/full extension) | 100 % |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Drawer usable width × usable depth in G | 26×20G |
| Type of product | Drawer |

Accessories

| | |
|---|-----------|
| One-hand individual drawer release system Drawer usable width in G 26 | 951020 26 |
| Pack of PVC covers for handles 10 pieces Drawer usable width in G 26 | 951032 26 |
| Labelling strip set 10 pieces Drawer usable width in G 26 | 951030 26 |
| Handle end caps 20 pieces Type 10 | 951025 10 |