

uvex**Safety helmet uvex pheos E-WR, Colour: YELLOW****Order data**

Order number	097808 YELLOW
GTIN	4031101523675
Item class	04U

Description**Version:**

Lightweight safety helmet in sporty design with closed helmet shell (without ventilation) for use in the electrician's range **up to 1,000 V AC**. The adapter system permits combination with visors, helmet ear defenders and helmet lamps. Protection against sprays of liquid metal (MM). Cold-resistant down to -30 °C.

- **6-point strap attachment**
- **30 mm Euro slot mounting**
- **PU sweatband**
- **Reaches well down on to the neck**
- **With rotary catch**

Standard:

DIN EN 397; DIN EN 50365

Specification:

Protection against sprayed liquid metal (MM), and cold-resistant down to -30 °C.

Helmet characteristics: Protection against liquid metal spraying out

Material of helmet shell: HDPE

Width adjustment: Drejelukning

Size: 52 - 61 cm

Weight: 401 g

Technical description

Colour	YELLOW
Resistance to cold	up to -30 °C
6-point textile support	yes
Headlight attachment possible	yes
Approval up to V	1000 V AC
Weight	401 g
Width adjustment	Drejelukning
Clips for attaching accessories	yes
Size	52 - 61 cm
Helmet characteristics	Electrical insulation
Helmet characteristics	Safety characteristics down to -30 °C
Helmet characteristics	Protection against liquid metal spraying out
Material of helmet shell	HDPE
Standard	DIN EN 397
Standard	DIN EN 50365
Type of product	Safety helmet

Accessories

Ear defenders Peltor™ X series helmet version Type X3	097756 X3
Ear defenders Peltor™ X series helmet version Type X4	097756 X4
Ear defenders Peltor™ X series helmet version Type X1	097756 X1
Ear defenders Peltor™ Optime™ helmet series Type 3	097753 3
Ear defenders Peltor™ Optime™ helmet series Type 1	097753 1
Ear defenders Peltor™ X series helmet version Type X5	097756 X5
Ear defenders Peltor™ X series helmet version Type X2	097756 X2
Ear defenders Peltor™ Optime™ helmet series Type 2	097753 2