


Garant GRIDLINE

## Drawer with one-handed individual drawer release system, 75 kg, 36×20G, Drawer front height: 250mm



### Order data

Order number	930744 250
GTIN	4062406131647
Item class	9GK

### Description

#### Version:

**100% full extension drawers** with differential runners. Aluminium handle with labelling strips that can be exchanged and rewritten.

Slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

With **individual drawer release system** prevents the opening of drawers during transport.

Absolutely necessary for all roller cabinets.

Load capacity 75 kg.

#### Suitable for:

Tool cabinet casing 40×24G No. 930735.

#### Supplied with:

Drawers each complete with 1 pair drawer runner rails.

#### Colour:

Drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

### Technical description

Usable height	225 mm
Front height	250 mm
Drawer usable area in G	36×20
Weight	22 kg
Individual drawer release system	One-hand

Drawer/pull-out shelf load capacity	75 kg
Usable depth in G	20
Usable width in G	36
Application range	Assembly trolley
Usable width	900 mm
Usable depth	500 mm
with individual drawer release system	yes
Material thickness	1.2 mm
Drawer runner extension (partial/full extension)	100 %
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	36×20G
Type of product	Drawer

## Accessories

Pack of PVC covers for handles 10 pieces Drawer usable width in G 36	951032 36
Handle end caps 20 pieces Type 10	951025 10
Labelling strip set 10 pieces Drawer usable width in G 36	951030 36
One-hand individual drawer release system Drawer usable width in G 36	951020 36