

Garant GRIDLINE

**Drawer with one-handed individual drawer release system, 75 kg, 20×24G,  
Drawer front height: 125mm****Order data**

Order number	931046 125
GTIN	4062406131869
Item class	9GK

**Description****Version:**

**100% full extension drawers** with differential runners. Aluminium handle with labelling strips that can be exchanged and rewritten.

Slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

With **individual drawer release system** prevents the opening of drawers during transport.

Absolutely necessary for all roller cabinets.

Load capacity 75 kg.

**Suitable for:**

Tool cabinet casing 24×28G No. 931035.

**Supplied with:**

Drawers each complete with 1 pair drawer runner rails.

**Colour:**

Drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Technical description**

Front height	125 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer usable area in G	20×24
Weight	14 kg

Usable height	100 mm
Usable depth in G	24
Usable width in G	20
Application range	Assembly trolley
Usable width	500 mm
Usable depth	600 mm
with individual drawer release system	yes
Material thickness	1.2 mm
Drawer runner extension (partial/full extension)	100 %
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	20×24G
Type of product	Drawer

## Accessories

Labelling strip set 10 pieces Drawer usable width in G 20	951030 20
Pack of PVC covers for handles 10 pieces Drawer usable width in G 20	951032 20
One-hand individual drawer release system Drawer usable width in G 20	951020 20
Handle end caps 20 pieces Type 10	951025 10