


Garant GRIDLINE

## Drawer with one-handed individual drawer release system, 75 kg, 26×24G, Drawer front height: 150mm



### Order data

Order number	931166 150
GTIN	4062406132026
Item class	9GK

### Description

#### Version:

**100% full extension drawers** with differential runners. Aluminium handle with labelling strips that can be exchanged and rewritten.

Slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

With **individual drawer release system** prevents the opening of drawers during transport.

Absolutely necessary for all roller cabinets.

Load capacity 75 kg.

#### Suitable for:

Tool cabinet casing 30×28G No. 931155.

#### Supplied with:

Drawers each complete with 1 pair drawer runner rails.

#### Colour:

Drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

### Technical description

Weight	17 kg
Drawer usable area in G	26×24
Front height	150 mm
Usable height	125 mm

Individual drawer release system	One-hand
Drawer/pull-out shelf load capacity	75 kg
Usable width in G	26
Usable depth in G	24
Application range	Assembly trolley
Usable width	650 mm
Usable depth	600 mm
with individual drawer release system	yes
Material thickness	1.2 mm
Drawer runner extension (partial/full extension)	100 %
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	26×24G
Type of product	Drawer

## Accessories

Pack of PVC covers for handles 10 pieces Drawer usable width in G 26	951032 26
Handle end caps 20 pieces Type 10	951025 10
One-hand individual drawer release system Drawer usable width in G 26	951020 26
Labelling strip set 10 pieces Drawer usable width in G 26	951030 26