


Garant GRIDLINE

Drawer with one-handed individual drawer release system, 75 kg, 26×24G, Drawer front height: 125mm



Order data

Order number	931166 125
GTIN	4062406132019
Item class	9GK

Description

Version:

100% full extension drawers with differential runners. Aluminium handle with labelling strips that can be exchanged and rewritten.

Slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

With **individual drawer release system** prevents the opening of drawers during transport.

Absolutely necessary for all roller cabinets.

Load capacity 75 kg.

Suitable for:

Tool cabinet casing 30×28G No. 931155.

Supplied with:

Drawers each complete with 1 pair drawer runner rails.

Colour:

Drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Weight	15 kg
Drawer usable area in G	26×24
Individual drawer release system	One-hand
Drawer/pull-out shelf load capacity	75 kg
Front height	125 mm

Usable height	100 mm
Usable width in G	26
Usable depth in G	24
Application range	Assembly trolley
Usable depth	600 mm
Usable width	650 mm
with individual drawer release system	yes
Material thickness	1.2 mm
Drawer runner extension (partial/full extension)	100 %
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	26×24G
Type of product	Drawer

Accessories

Labelling strip set 10 pieces Drawer usable width in G 26	951030 26
One-hand individual drawer release system Drawer usable width in G 26	951020 26
Handle end caps 20 pieces Type 10	951025 10
Pack of PVC covers for handles 10 pieces Drawer usable width in G 26	951032 26