


Garant GRIDLINE

Drawer with one-handed individual drawer release system, 200 kg, 36×24G, Drawer front height: 250mm



Order data

Order number	931356 250
GTIN	4062406132262
Item class	9GK

Description

Version:

100% full extension drawers with differential runners. Aluminium handle with labelling strips that can be exchanged and rewritten.

Slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

With **individual drawer release system** prevents the opening of drawers during transport.

Absolutely necessary for all roller cabinets.

Load capacity 200 kg.

Suitable for:

Tool cabinet casing 40×28G No. 931335.

Supplied with:

Drawers each complete with 1 pair drawer runner rails.

Colour:

Drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Individual drawer release system	One-hand
Front height	250 mm
Drawer usable area in G	36×24
Drawer/pull-out shelf load capacity	200 kg

Weight	24 kg
Usable height	225 mm
Usable depth in G	24
Usable width in G	36
Application range	Assembly trolley
Usable width	900 mm
Usable depth	600 mm
with individual drawer release system	yes
Material thickness	1.2 mm
Drawer runner extension (partial/full extension)	100 %
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	36×24G
Type of product	Drawer

Accessories

Pack of PVC covers for handles 10 pieces Drawer usable width in G 36	951032 36
Labelling strip set 10 pieces Drawer usable width in G 36	951030 36
Handle end caps 20 pieces Type 10	951025 10
One-hand individual drawer release system Drawer usable width in G 36	951020 36