

**Pair of gloves Cut E, Glove size: 7****Order data**

Order number	094613 7
GTIN	4062406132415
Item class	02H

Description**Version:**

Gloves with new fibre technology **completely without glass fibres or steel fibres**. Coating of nitrile foam. Oeko-Tex Standard 100.

HOLEX Cut E. Cut-resistant gloves with cut protection level E and 15-gauge knitting technology for variable activities with extreme cut hazards.

Version of the advertising text:

Gloves with new DYTEC® fibre technology **completely without glass fibres or steel fibres**. Coating of nitrile foam. Oeko-Tex Standard 100.

15-gauge knitting technology for variable activities with extreme cut hazards.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Note re advertising text:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Protection category	Category II
Type of glove	Cut-resistant gloves
Glove size	7
Knitted technology	15G
Clothing standard	Oeko-Tex Standard 100
EN 388	4443E
Backing material	DYTEC
Coating	Nitrile foam
Coating variant	The palms of the hands
Application range	All-round
Colour	black / grey
Application	reusable
Cut protection class	E
Type of product	Cut-resistant gloves