

**HOLEX****Pair of gloves Cut F / A8, Glove size: 7****Order data**

Order number	094615 7
GTIN	4062406132569
Item class	02H

**Description****Version:**

Gloves with new fibre technology **completely without glass fibres or steel fibres**. Coating of nitrile foam. Oeko-Tex Standard 100.

HOLEX Cut F. Cut-resistant gloves with the highest EN-ISO cut protection level F (equivalent to ANSI A8) for heavy-duty activities with extreme cut hazards.

**Version of the advertising text:**

Gloves with new DYTEC® fibre technology **completely without glass fibres or steel fibres**. Coating of nitrile foam. Öko-Tex Standard 100.

Cut protection level F (equivalent to ANSI A8) for variable activities with extreme cut hazards.

**Standard:**

EN 388; EN ISO 21420

**Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

**Note re advertising text:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

**Technical description**

Type of glove	Cut-resistant gloves
Protection category	Category II
Glove size	7
Knitted technology	10G
Clothing standard	Oeko-Tex Standard 100
EN 388	4543F
Backing material	DYTEC
Coating	Nitrile foam
Coating variant	The palms of the hands
Application range	Heavy Duty
Colour	black / grey
Application	reusable
Cut protection class	F
Type of product	Cut-resistant gloves