

HOLEX**Pair of gloves Cut F / A6, Glove size: 8****Order data**

Order number	094614 8
GTIN	4062406132521
Item class	02H

Description**Version:**

Gloves with new fibre technology **completely without glass fibres or steel fibres**. Coating of nitrile foam. Oeko-Tex Standard 100.

HOLEX Cut F. Cut-resistant gloves with the highest EN-ISO cut protection level F (equivalent to ANSI A6) and 13-gauge knitting technology for heavy-duty activities with extreme cut hazards.

Version of the advertising text:

Gloves with new DYTEC® fibre technology **completely without glass fibres or steel fibres**. Coating of nitrile foam. Oeko-Tex Standard 100.

Cut protection level F (equivalent to ANSI A6) for variable activities with extreme cut hazards.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Note re advertising text:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Type of glove	Cut-resistant gloves
Glove size	8
Protection category	Category II
Knitted technology	13G
Clothing standard	Oeko-Tex Standard 100
EN 388	4543F
Backing material	DYTEC
Coating	Nitrile foam
Coating variant	The palms of the hands
Application range	All-round
Colour	black / grey
Application	reusable
Cut protection class	F
Type of product	Cut-resistant gloves