

HOLEX
Pair of gloves Cut F / A8, Glove size: 11

Order data

Order number	094615 11
GTIN	4062406132606
Item class	02H

Description
Version:

Gloves with new fibre technology **completely without glass fibres or steel fibres**. Coating of nitrile foam. Oeko-Tex Standard 100.

HOLEX Cut F. Cut-resistant gloves with the highest EN-ISO cut protection level F (equivalent to ANSI A8) for heavy-duty activities with extreme cut hazards.

Version of the advertising text:

Gloves with new DYTEC® fibre technology **completely without glass fibres or steel fibres**. Coating of nitrile foam. Öko-Tex Standard 100.

Cut protection level F (equivalent to ANSI A8) for variable activities with extreme cut hazards.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Note re advertising text:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Type of glove	Cut-resistant gloves
Glove size	11
Protection category	Category II
Knitted technology	10G
Clothing standard	Oeko-Tex Standard 100
EN 388	4543F
Backing material	DYTEC
Coating	Nitrile foam
Coating variant	The palms of the hands
Application range	Heavy Duty
Colour	black / grey
Application	reusable
Cut protection class	F
Type of product	Cut-resistant gloves