


Garant GRIDLINE

Drawer with one-handed individual drawer release system, 200 kg, 46×24G, Drawer front height: 125mm



Order data

Order number	931456 125
GTIN	4062406132637
Item class	9GK

Description

Version:

100% full extension drawers with differential runners. Aluminium handle with labelling strips that can be exchanged and rewritten.

Slots at 50-mm/2G intervals to take slotted dividers (from drawer front height 75 mm).

With **individual drawer release system** prevents the opening of drawers during transport.

Absolutely necessary for all roller cabinets.

Load capacity 200 kg.

Suitable for:

Tool cabinet casing 50×28G No. 931435.

Supplied with:

Drawers each complete with 1 pair drawer runner rails.

Colour:

Drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Only GridLine divider inserts can be used in the widths 2G, 4G, 6G, 8G, 10G or 12 G.

Technical description

Drawer usable area in G	46×24
Usable height	100 mm
Front height	125 mm
Individual drawer release system	One-hand

Drawer/pull-out shelf load capacity	75 kg
Weight	22 kg
Usable depth in G	24
Usable width in G	46
Application range	Assembly trolley
Usable width	1150 mm
Usable depth	600 mm
with individual drawer release system	yes
Material thickness	1.2 mm
Drawer runner extension (partial/full extension)	100 %
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	46×24G
Type of product	Drawer

Accessories

Pack of PVC covers for handles 10 pieces Drawer usable width in G 46	951032 46
Handle end caps 20 pieces Type 10	951025 10
Labelling strip set 10 pieces Drawer usable width in G 46	951030 46
One-hand individual drawer release system Drawer usable width in G 46	951020 46