

Mitutoyo
External blade micrometer, Measuring range: 0-25 mm

Order data

Order number	421895 0-25
GTIN	4946368012605
Item class	44A

Description
Version:

With non-rotating spindle and flat blade anvils. Measuring spindle and anvil of hardened steel, controls and reading parts satin chrome-plated.

Supplied with:

From size 25-50 including 1 setting standard.

Packaging: sturdy box

Micrometer barrel graduations: 1/50 mm

Calibration: B1

Scale divisions: 0.01 mm

Spindle Ø: 8 mm

Spindle pitch: 0.5 mm

Flat blade anvils width: 0.75 mm

Flat blade anvils length: 6.5 mm

Technical description

Scale divisions	0.01 mm
Micrometer barrel graduations	1/50 mm
Spindle Ø	8 mm
Flat blade anvils length	6.5 mm
Flat blade anvils width	0.75 mm
Calibration	B1

Spindle pitch	0.5 mm
Standard	DIN 863
Measurement technology	analogue
Packaging	sturdy box
Type of product	Special external micrometer

Services

DAkkS calibration External micrometer maximum measuring range 100 mm	012060 100
Calibration External tube micrometer maximum measuring range 25 mm	012050 25