

**Mitutoyo**
**External blade micrometer, Measuring range: 25-50 mm**

**Order data**

Order number	421895 25-50
GTIN	4946368012612
Item class	44A

**Description**
**Version:**

With non-rotating spindle and flat blade anvils. Measuring spindle and anvil of hardened steel, controls and reading parts satin chrome-plated.

**Supplied with:**

From size 25-50 including 1 setting standard.

Packaging: sturdy box

Micrometer barrel graduations: 1/50 mm

Calibration: B1

Calibration: B2

Scale divisions: 0.01 mm

Spindle Ø: 8 mm

Spindle pitch: 0.5 mm

Flat blade anvils width: 0.75 mm

Flat blade anvils length: 6.5 mm

**Technical description**

Calibration	B1
Calibration	B2
Micrometer barrel graduations	1/50 mm
Spindle Ø	8 mm
Flat blade anvils length	6.5 mm

Spindle pitch	0.5 mm
Flat blade anvils width	0.75 mm
Scale divisions	0.01 mm
Standard	DIN 863
Measurement technology	analogue
Packaging	sturdy box
Type of product	Special external micrometer

### Services

Calibration Micrometer standard for external micrometer maximum nominal size 100 mm	012110 100
Calibration External tube micrometer maximum measuring range 100 mm	012050 100
DAkkS calibration External micrometer maximum measuring range 100 mm	012060 100