



Cordless drill/driver without rechargeable battery and charger, Type: 71161264



Order data

Order number	070200 71161264
GTIN	4014586889900
Item class	03F

Description

Version:

2 and 4 speed cordless drill/driver

- For precise drilling and screwdriving results.
- Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.
- Sturdy metal gearbox for long working life.
- Good weight balance and ergonomics with softgrip inserts for non-tiring continuous work.
- Maximum work progress with AMPShare 18V ProCore rechargeable batteries: COOLPACK 2.0 technology provides 135% longer battery life. State-of-the-art cell technology and intelligent battery management provide 87% more power than conventional batteries.

Advantage:

Patented 4-speed gearbox.

Supplied with:

Without battery and charger. Supplied with drill chuck, belt clip and transport case. **Without battery and without charger.**

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Note:

See No. 073851 – 073866 for suitable batteries, chargers and starter sets.

Technical description

Packaging	Carrying case
Weight	1.2 kg
typical application	Heavy Duty
Manufacturer's designation	ASCM 18 QSW Select
Motor design	Brushless motor
maximum speed 3rd speed	1400 min ⁻¹
Battery voltage	18 V
maximum speed 2nd speed	700 min ⁻¹
maximum vibration to EN	<2.5 m/s ²
maximum twist drill size Ø in wood	40 mm
maximum torque soft	20 Nm
maximum speed 4th speed	2500 min ⁻¹
maximum speed 1st speed	400 min ⁻¹
suitable battery - supplier / battery type / voltage	Fein type E 18 V
Quick-clamping chuck range	1.5 - 13 mm
maximum twist drill size Ø in steel	13 mm
maximum torque hard	40 Nm
Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Suitable for material	wood
Suitable for material	Steel
Type of product	Drill/driver
USP1	4-speed gearbox. 18V

USP2

Suitable for wood & steel, quick-release chuck clamping range 1.5-13, without rechargeable battery

Accessories

Li-ion battery Rechargeable battery type, battery voltage FE18 V

073835 FE18