



Cordless drill/driver without rechargeable battery and charger, Type: 711SET



Order data

| | |
|--------------|---------------|
| Order number | 070200 711SET |
| GTIN | 2050002046481 |
| Item class | 03F |

Description

Version:

2 and 4 speed cordless drill/driver

- For precise drilling and screwdriving results.
- Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.
- Sturdy metal gearbox for long working life.
- Good weight balance and ergonomics with softgrip inserts for non-tiring continuous work.
- Maximum work progress with AMPShare 18V ProCore rechargeable batteries: COOLPACK 2.0 technology provides 135% longer battery life. State-of-the-art cell technology and intelligent battery management provide 87% more power than conventional batteries.

Advantage:

Patented 4-speed gearbox.

Supplied with:

Without battery and charger. Comprehensive **professional thread tapping set** ideal for metalworking.

- **QuickIN bit holder (1/4 inch).**
- **QuickIN tapping adapter with 2 collets.**
- **QuickIN socket adapter.**

- **Angle head.**
- **Charger and 2 x batteries.**

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Note:

See No. 073851 – 073866 for suitable batteries, chargers and starter sets.

Technical description

| | |
|--|------------------------------|
| Battery capacity | 6 Ah |
| maximum vibration to EN | <2.5 m/s ² |
| Packaging | Carrying case |
| maximum torque soft | 46 Nm |
| maximum speed 1st speed | 400 min ⁻¹ |
| typical application | Heavy Duty |
| maximum speed 2nd speed | 800 min ⁻¹ |
| Weight | 2 kg |
| Quick-clamping chuck range | 1.5 - 13 mm |
| maximum speed 4th speed | 3850 min ⁻¹ |
| maximum speed 3rd speed | 1950 min ⁻¹ |
| maximum twist drill size Ø in wood | 50 mm |
| maximum twist drill size Ø in steel | 25 mm |
| Battery voltage | 18 V |
| maximum torque hard | 90 Nm |
| Motor design | Brushless motor |
| Manufacturer's designation | ASCM 18 QMSET |
| suitable battery - supplier / battery type / voltage | Fein type E 18 V |
| Number of rechargeable batteries contained | 2 |
| Type of rechargeable battery | Lithium-ion |
| Power supply | Rechargeable battery-powered |
| Suitable for material | wood |
| Suitable for material | Steel |

| | |
|-----------------|--|
| Type of product | Drill/driver |
| USP1 | 4-speed gearbox. 18V |
| USP2 | Suitable for wood & steel, quick-release chuck clamping range 1.5-13, without rechargeable battery |

Accessories

| | |
|---|-----------------|
| Li-ion batteryHighPower Battery type, battery voltage FE18 V | 073834 FE18 |
| Accessories for hand-held screwdriversQuick-In Type 711301 | 070208 711301 |
| Cordless drill/driverwithout rechargeable battery and charger Type 71161164 | 070200 71161164 |
| Battery starter set Type 92604323 | 073832 92604323 |