



Cordless impact wrench / driver, Type: 71150764



Order data

Order number	074000 71150764
GTIN	4014586887449
Item class	03F

Description

Version:

Powerful cordless impact wrench with **brushless motor and torque adjustment in 6 steps**. Robust all-metal impact drive and ergonomic handling thanks to soft-grip coating.

- **1/4 inch HEX bit direct drive socket.**
- **210 Nm maximum torque.**
- **Select Version with MultiVolt interface for all FEIN Li-ion batteries (12-18 V).**

Advantage:

Electronic torque adjustment in 6 steps.

Supplied with:

Version without battery and without charger, including L-BOXX. **Without battery and without charger**, with carrying case.

Note:

See No. 073851 – 073866 for suitable batteries, chargers and starter sets.

Technical description

Packaging	Carrying case
maximum torque	210 Nm

maximum vibration to EN	6 m/s ²
Tool arbor size	1/4 in
typical application	Heavy Duty
Manufacturer's designation	ASCD 18-200 W4
Tool arbor drive profile	HEX
Number of impacts	0 - 3000 min ⁻¹
suitable battery - supplier / battery type / voltage	Fein type E 18 V
Battery voltage	12 V
Battery voltage	18 V
Weight	1 kg
Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Suitable for material	Steel
Type of product	Impact wrench

Accessories

Li-ion battery Rechargeable battery type, battery voltage FE12 V	073835 FE12
Li-ion battery Rechargeable battery type, battery voltage FE18 V	073837 FE18
Li-ion battery Rechargeable battery type, battery voltage FE18 V	073835 FE18
Li-ion battery Rechargeable battery type, battery voltage FE12 V	073837 FE12