



## Torque shut-off screwdriver with ParameterControl Centre handle screwdriver, Type: 7112786



### Order data

Order number	071111 7112786
GTIN	4014586891446
Item class	03F

### Description

#### Version:

**FEIN ACCU TEC shut-off screwdrivers** are designed for the most demanding applications requiring **precise screw tightening in series production**.

- **Brushless EC motors with working life extended by a factor of several times and up to 80 % lower maintenance costs.**
- **Restart delay after the screw tightening, to avoid "follow-up".**
- **Restart inhibit if the remaining battery charge is insufficient to perform the screw tightening.**
- **Tight screw tightening tolerances for high screw tightening quality.**
- **Precise and consistent tightening torques in any screw tightening application.**
- **Testable screwdrivers, CmK-value > 1.67 ±10% (based on 6 sigma) to ISO 5393 VDI/VDE 2647.**

**The release torque is 25 % above the tightening torque.**

Torque shut-off screwdriver with ParameterControl for easy and individual programming on a PC , using the programming adaptor (No. 071135 size 92604163).

**Freely programmable parameters:** Speed, direction of rotation, angle of rotation, torque threshold and time.

Up to 5 programmable steps. Precise configuration for each screw tightening application. **Final switch-off by mechanical clutch.** Ideal for optimising the process and time.

**Shut-off screwdriver, takes a Li-ion battery. Maintenance-free** up to 500,000 screw fastenings.

**Supplied with:**

Just the screwdriver itself is supplied, **without battery, charger or setting tool and angle head.** Please order the battery, charger, setting tool and angle head specifically for the device.

**Note:**

See No. 073832 ff. for suitable rechargeable batteries and chargers.

You can find torque analysers from No. 654300. See No. 654381 for torque sensors / rotational angle sensors. Torque pre-setting service on request.

## Technical description

Weight including rechargeable battery	0.8 kg
Manufacturer's designation	ASM 18-8 PC
Toolholder	1/4 inch HEX (E 6.3)
Speed range	110 - 1200 min <sup>-1</sup>
Torque range	1 - 8 Nm
Battery voltage	12 V
Battery voltage	18 V
suitable battery - supplier / battery type / voltage	Fein type E 12 V
suitable battery - supplier / battery type / voltage	Fein type E 18 V
Format	Centre handle screwdriver
Power supply	Rechargeable battery-powered
Type of product	Screwdriver

## Accessories

Electronic torque tool tester"TTT"	654340
Electronic torque screwdriver tester"TST" maximum torque 2 N·m	654300 2
Li-ion battery Rechargeable battery type, battery voltage FE18 V	073835 FE18

Li-ion battery Rechargeable battery type, battery voltage  
FE18 V

073837 FE18

Electronic torque screwdriver tester "TST" maximum torque  
10 N·m

654300 10

Electronic torque screwdriver tester "TST" maximum torque  
25 N·m

654300 25