



Torque shut-off screwdriver with ParameterControl Centre handle screwdriver, Type: 7112796



Order data

Order number	071111 7112796
GTIN	4014586891460
Item class	03F

Description

Version:

FEIN ACCU TEC shut-off screwdrivers are designed for the most demanding applications requiring **precise screw tightening in series production**.

- **Brushless EC motors with working life extended by a factor of several times and up to 80 % lower maintenance costs.**
- **Restart delay after the screw tightening, to avoid "follow-up".**
- **Restart inhibit if the remaining battery charge is insufficient to perform the screw tightening.**
- **Tight screw tightening tolerances for high screw tightening quality.**
- **Precise and consistent tightening torques in any screw tightening application.**
- **Testable screwdrivers, CmK-value > 1.67 ±10% (based on 6 sigma) to ISO 5393 VDI/VDE 2647.**

The release torque is 25 % above the tightening torque.

Torque shut-off screwdriver with ParameterControl for easy and individual programming on a PC , using the programming adaptor (No. 071135 size 92604163).

Freely programmable parameters: Speed, direction of rotation, angle of rotation, torque threshold and time.

Up to 5 programmable steps. Precise configuration for each screw tightening application. **Final switch-off by mechanical clutch.** Ideal for optimising the process and time.

Shut-off screwdriver, takes a Li-ion battery. Maintenance-free up to 500,000 screw fastenings.

Supplied with:

Just the screwdriver itself is supplied, **without battery, charger or setting tool and angle head.** Please order the battery, charger, setting tool and angle head specifically for the device.

Note:

See No. 073832 ff. for suitable rechargeable batteries and chargers.

You can find torque analysers from No. 654300. See No. 654381 for torque sensors / rotational angle sensors. Torque pre-setting service on request.

Technical description

Battery voltage	12 V
Battery voltage	18 V
Weight including rechargeable battery	0.8 kg
Speed range	80 - 900 min ⁻¹
Manufacturer's designation	ASM 18-12 PC
Torque range	4 - 12 Nm
Format	Centre handle screwdriver
suitable battery - supplier / battery type / voltage	Fein type E 12 V
suitable battery - supplier / battery type / voltage	Fein type E 18 V
Toolholder	1/4 inch HEX (E 6.3)
Power supply	Rechargeable battery-powered
Type of product	Screwdriver

Accessories

Electronic torque screwdriver tester "TST" maximum torque 10 N·m	654300 10
Electronic torque screwdriver tester "TST" maximum torque 25 N·m	654300 25
	654300 2

Electronic torque screwdriver tester "TST" maximum torque
2 N·m

Electronic torque tool tester "TTT"

654340

Li-ion battery Rechargeable battery type, battery voltage
FE18 V

073837 FE18

Li-ion battery Rechargeable battery type, battery voltage
FE18 V

073835 FE18