

**Bi-metal hole saw set Power Change Plus, Type: 19-83****Order data**

Order number	589810 19-83
GTIN	3165140949590
Item class	54B

Description**Version:**

Bi-metal hole saw set with Power Change Plus system in popular diameters. With hexagonal drive shank and HSS centre drill; in a plastic case.

Technical description

Number of centre drills	2
Number of pieces	9
Hole saw \varnothing	19; 25; 38; 44; 68; 83 mm
Number of mounting shafts	1
Series	Power Change Plus
Type of product	Hole saw

Accessories

Hole saw bi-metalPower Change Plus Diameter 105 mm	589790 105
Hole saw bi-metalPower Change Plus Diameter 121 mm	589790 121
Hole saw bi-metalPower Change Plus Diameter 152 mm	589790 152
Hole saw bi-metalPower Change Plus Diameter 16 mm	589790 16
Hole saw bi-metalPower Change Plus Diameter 19 mm	589790 19
Hole saw bi-metalPower Change Plus Diameter 20 mm	589790 20
Hole saw bi-metalPower Change Plus Diameter 22 mm	589790 22
Hole saw bi-metalPower Change Plus Diameter 25 mm	589790 25
Hole saw bi-metalPower Change Plus Diameter 29 mm	589790 29
Hole saw bi-metalPower Change Plus Diameter 32 mm	589790 32
Hole saw bi-metalPower Change Plus Diameter 35 mm	589790 35
Hole saw bi-metalPower Change Plus Diameter 38 mm	589790 38
Hole saw bi-metalPower Change Plus Diameter 40 mm	589790 40
Hole saw bi-metalPower Change Plus Diameter 44 mm	589790 44
Hole saw bi-metalPower Change Plus Diameter 51 mm	589790 51
Hole saw bi-metalPower Change Plus Diameter 54 mm	589790 54
Hole saw bi-metalPower Change Plus Diameter 60 mm	589790 60
Hole saw bi-metalPower Change Plus Diameter 65 mm	589790 65
Hole saw bi-metalPower Change Plus Diameter 68 mm	589790 68
Hole saw bi-metalPower Change Plus Diameter 76 mm	589790 76
Hole saw bi-metalPower Change Plus Diameter 83 mm	589790 83
Hole saw bi-metalPower Change Plus Diameter 92 mm	589790 92
Drive shankPower Change Plus hexagonal suitable for hole saw Ø 14-152 mm	589795 14-152
Centre drillPower Change Plus Type HSS-CO	589800 HSS-CO