



Cordless drill/driver, Type: 7113226H1



Order data

Order number	070205 7113226H1
GTIN	2050002046511
Item class	03F

Description

Version:

2 and 4 speed cordless drill/driver

- For precise drilling and screwdriving results.
- Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.
- Sturdy metal gearbox for long working life.
- Good weight balance and ergonomics with softgrip inserts for non-tiring continuous work.
- Maximum work progress with AMPShare 18V ProCore rechargeable batteries: COOLPACK 2.0 technology provides 135% longer battery life. State-of-the-art cell technology and intelligent battery management provide 87% more power than conventional batteries.

Cordless 2-speed drill / driver

- Low-maintenance POWER-Drive EC DC motor with high torque and overload protection.
- Mechanical torque cut-out adjustable, in 22 steps, additional drilling step.

Advantage:

Mechanical torque adjustment in 22 steps.

Supplied with:

Supplied with battery and charger. Supplied with drill chuck, belt clip, transport case and charger.

Technical description

Quick-clamping chuck range	1.5 - 13 mm
maximum twist drill size Ø in wood	50 mm
maximum vibration to EN	<2.5 m/s ²
Motor design	Brushless motor
Weight	1.7 kg
Battery capacity	3 Ah
typical application	Strong
maximum speed 1st speed	450 min ⁻¹
suitable battery - supplier / battery type / voltage	Fein type E 18 V
Battery voltage	18 V
maximum torque soft	32 Nm
maximum speed 2nd speed	2000 min ⁻¹
Manufacturer's designation	ABS 18 QC
maximum twist drill size Ø in steel	13 mm
maximum torque hard	60 Nm
Packaging	Carrying case
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Suitable for material	Steel
Suitable for material	wood
Type of product	Drill/driver
USP1	18V, 2-speed
USP2	Quick-release chuck clamping range 1.5-13, in a carrying case

Accessories

Li-ion battery Rechargeable battery type, battery voltage FE18 V	073837 FE18
Battery starter set Type 92604324	073832 92604324
Cordless drill/driver Type 71132264	070205 71132264