

**Mitutoyo**
**Digital caliper with AOS system and data output, Measuring range: 300mm**

**Order data**

Order number	412642 300
GTIN	4946368728384
Item class	44A

**Description**
**Version:**

Measured result is displayed in easy-to-read characters (height 9 mm). The **AOS (Advanced Onsite Sensor)** electromagnetic measurement system offers enhanced protection against water and dust.

- **Absolute scale, no zeroing necessary, resulting in faster, more reliable measuring.**
- **Low power consumption (20,000 hours continuous use), battery charge indicator**

**Supplied with:**

1 battery No. 081560 size 357.

**Optional extras:**

Data cables No. 497080 and No. 497100 with data button.

Battery compartment cover No. 412239 size B.

**Technical description**

Depth gauge available	yes
Jaw length	64 mm
Number of batteries contained	1
Measuring range	0 - 300 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Calibration	A1
Standard	ISO 13385
Scale divisions	0.01 mm

Digit height LCD display	9 mm
Depth gauge	rectangular 3.7×1.4
Working time	20000 h
Battery type	Button cell
Power supply	Battery-powered
Measurement deviation E MPE	±0.03 mm
Interface	USB interface
Interface	Digimatic interface
Measurement method of the measuring instrument	electro-magnetic inductive procedure
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

## Services

DAkkS calibrationCalipers / depth gauges maximum measuring range 300 mm	021010 300
CalibrationCalipers / depth gauges maximum measuring range 300 mm	021000 300

## Accessories

Battery compartment cover Type B	412239 B
----------------------------------	----------