

JEPSON POWER**Metal cutting circular saw, Type: 9435****Order data**

Order number	078231 9435
GTIN	27168943512
Item class	07E

Description**Version:**

Powerful metal cutting circular saws for sawing sheet metal, sandwich panels, metal plates, tubes and sections of steel, non-ferrous metals, and composite materials **without generating sparks.**

- **No need to use cooling lubricants.**
- **No reworking necessary.**
- **Cuts in seconds.**

Metal cutting circular saw Premium Super DRY Cutter 9435.

- **Ideal for sawing pipes and profiles made from stainless steel, steel, non-ferrous metals, plastics and composite materials.**
- **Vibration damper for high safety and a long working life.**
- **Precision quick-clamping system for mitre cuts.**
- **Optionally with sturdy table mounting stand with length stop (No. 078238).**

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

Supplied with:

Supplied with 1 × saw blade 90Z No. 078237 size 90 for steel, stainless steel, NF metals.

Note:

Metal cutting circular saw DRY MITER Cutter 9410ND for delicate sawing in soft and delicate material available on request.

Manufacturer's designation: 9435

Power consumption: 2400 W

maximum speed: 1400 min⁻¹

Saw blade Ø: 355 mm

maximum cutting depth 90°: 140 mm

maximum cutting depth 45°: 102 mm

Technical description

Manufacturer's designation	9435
maximum speed	1400 min ⁻¹
Saw blade Ø	355 mm
maximum cutting depth 45°	102 mm
Mains frequency	50 Hz
maximum cutting depth 90°	140 mm
Weight	25 kg
Power consumption	2400 W
AC supply voltage	230 V
Power supply	Mains operated
Type of product	Saw

Accessories

Drytec® carbide circular saw blade Ø 355×25.4 mm Number of teeth 60	078237 60
Carbide circular saw blade only for stainless steel Ø 355×25.4 mm Number of teeth 90	078236 90
Drytec® carbide circular saw blade Ø 355×25.4 mm Number of teeth 72	078237 72
Stand for No. 078231 Type 600526	078238 600526
	078237 90

Drytec® carbide circular saw blade Ø 355×25.4 mm
Number of teeth 90
