

## Resistance measuring device, Type: RESIST



### Order data

Order number	473340 RESIST
GTIN	2050001865090
Item class	47F

### Description

#### Version:

Compact, easy to use SAFE-STAT resistance measuring device with two brass strips and connection option to external electrodes **for measuring surface, leakage and contact resistance according to IEC 61340**. Thanks to the integrated parallel electrodes on the underside, the measuring device only needs to be placed on the measuring point.

#### Supplied with:

Grounding conductor, cover and instruction manual.

#### Optional extras:

9 V block battery No. 081561 size. 6LR61.

Calibration: Price on request

Measuring range:  $10^3 - 10^{12} \Omega$

Error limit:  $\pm 1$  decade

Measuring voltage: 100 V

Length: 130 mm

Width: 70 mm

Height: 27 mm

### Technical description

Height	27 mm
--------	-------

Weight	217 g
Measuring voltage	100 V
Length	130 mm
Width	70 mm
Measuring range	$10^3 - 10^{12} \Omega$
Error limit	$\pm 1$ decade
Power supply	Battery-powered
Article no of the battery / rechargeable battery fitted	081561 6LR61
Battery type	9 V block
Number of batteries contained	1
Calibration	Price on request
Type of product	Resistance measuring device

---

## Accessories

Round electrode	473346
Alkaline-manganese batteries International size 6LR61	081556 6LR61