

Mitutoyo
Digital depth gauge AOS with data output, Measuring range: 150mm

Order data

Order number	418711 150
GTIN	4946368688503
Item class	44A

Description
Version:

Measured result is displayed in easy-to-read digits. The measuring faces are precision lapped.

Supplied with:

1 battery No. 081560 size 357.

Optional extras:

Data cables No. 497080 and 497100.

Technical description

Bridge length	100 mm
Calibration	A1
Scale divisions	0.01 mm
Interface	USB interface
Interface	Digimatic interface
Cross-section measuring beam	16x3.5 mm
Article no of the battery / rechargeable battery fitted	081560 357
Number of batteries contained	1
Power supply	Battery-powered
Measurement deviation E MPE	± 0.02 mm

Standard	ISO 13385
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	Wallet
Measurement method of the measuring instrument	electro-magnetic inductive procedure
Type of product	Depth gauge

Services

DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200
Calibration Calipers / depth gauges maximum measuring range 200 mm	021000 200

Accessories

Connecting cable with data switch Type D1	497100 D1
Single extension base Bridge length 180 mm	418744 180
Connecting cable Type D1	497080 D1
Connecting cable with data switch Type D2	497100 D2
Connecting cable with data switch Type USB2	497100 USB2
Receiver / USB keyboard interface Type	498965
Single extension base Bridge length 260 mm	418744 260
Connecting cable Type USB2	497080 USB2
Connecting cable Type D2	497080 D2
Button cell / special battery Battery type 357	081560 357
Transmitter Type S1	498966 S1
Multi-receiver / USB keyboard interface Type	498975
Single extension base Bridge length 320 mm	418744 320